

RUSH+ 2.0 DUO

INCLUSIVITY & SUSTAINABILITY

The RUSH+ 2.0, our iconic model, is designed to withstand the harshest work environments, making it a trusted choice for all professionals.

RUSH+ 2.0 DUO is specially engineered with unique lens technologies that give workers an edge over their duties. PLATINUM coated, with polarized, photochromatic or corrective lenses, RUSH+ 2.0 DUO ensures an optimal vision in all situations.

The frame is also made with 64% of recycled materials to reduce its carbon footprint.

41 G

- + **COMFORTABLE FIT: ERGONOMIC TEMPLES & HINGES**
- + **OPTIMISED CURVATION: PROTECTIVE WITH OPTIMISED POWER RANGE**
- + **GLOBAL SOLUTION: AVAILABLE IN BOTH PRESCRIPTION AND PLANO**
- + **SUSTAINABLE: MADE OF 64% RECYCLED MATERIAL**

bolle
SAFETY

AVAILABLE WITH
PRESCRIPTION

PART OF THE RUSH+ COLLECTION



TECHNOLOGIES

CSP
POLARIZED
MODULATOR
PLATINUM

VERSIONS



RUSDMN50E



RUSDMN60E

PRESCRIPTION



RUSDMX10E



RUSDMX11E

RUSH+ 2.0 DUO

USE	VERSION	REFERENCE	LENS MARKING	FRAME MARKING	COATING	STANDARD
	 SMOKE POLARIZED	 RUSDMN50E	 GL3 CT 1 KN C€	16321  G3 CT 1-M C€	 PLATINUM	EN ISO 16321-1
	 MODULATOR	 RUSDMN60E	 GLO-3 CT 1 KN C€	16321  G3 CT 1-M C€	 PLATINUM	EN ISO 16321-1

BOLLÉ SAFETY PRODUCT APPROVAL CERTIFICATES TO C€ STANDARDS WILL BE SENT ON REQUEST.

PACKAGING & EAN13 CODE

SINGLE: Size: 29.5 x 12 x 7 cm	INNER BOX: Size: 27.5x18x13 cm Weight: 0.78 kg	OUTER PACK: Size: 58 x 38 x 30 cm Weight: 6.5 kg
3660740023973	3660740123970 - 10 pcs	3660740223977 - 80 pcs
3660740024000	3660740124007 - 10 pcs	3660740224004 - 80 pcs
CUSTOM CODE: 9004901000		



GENERAL SPECIFICATIONS

LENS	POLYCARBONATE - 2 MM	FOAM	
CURVE	6 - CURVED	STRAP	
FRAME	RECYCLED PC/TPR - METAL BAR	SUPPLIED WITH	MICROFIBER POUCH

OPTIONAL ACCESSORIES

REFERENCE	DESCRIPTION	SINGLE	INNER BOX	OUTER PACK
PSPUNISS01	RETAINER STRAP	3660740011970	3660740111977 - 40 pcs	3660740211974 - 480 pcs

KNOW MORE
ABOUT
MARKINGS:

CLICK

OR SCAN:



CLEANING & STORAGE

CLEANING : The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE : Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE : All products must be stored in a dry and clean environment.



MADE IN: CN

DATASHEET: 10-14-2026

bolle-safety.com

Europe Headquarters
34 rue de la Soie
69100 Villeurbanne
France
P : 00 33 (0) 4 78 85 23 64

U.K. & Ireland
Unit C83 - Barwell Business Park
Leatherhead Road - Chessington
Surrey - KT9 2NY - UK
P : 00 44 (0)208 391 4700

USA Office
5355 Avenida Encinas, Suite 107
Carlsbad, CA 92008
United States of America
P : 800 222 6553

Asia-Pacific Office
32-40 Fairchild Street
Heatherton VIC 3202
Australia
P : 1300 138 098



THE PPE EYEWEAR
SPECIALISTS

RUSH+ 2.0 DUO |

USE	VERSION	FRAME COLOR	REFERENCE	SIZE	TEMPLES	FRAME MARKING	STANDARD
	 PRESCRIPTION FRAME	BLACK / GREY / CRYSTAL	 RUSDMX10E	58/17	130 mm	16321  UL3 CT 1-M 	EN ISO 16321-1
	 PRESCRIPTION FRAME	BLACK / GREY	 RUSDMX11E	58/17	130 mm	16321  G4 CT 1-M 	EN ISO 16321-1

BOLLÉ SAFETY PRODUCT APPROVAL CERTIFICATES TO  STANDARDS WILL BE SENT ON REQUEST.

PACKAGING & EAN13 CODE

SINGLE: Size: 6.3 x 19 x 8 cm Weight: 46 g	INNER BOX:	OUTER PACK (80): Size: 30 x 58 x 38 cm Weight: 6.95 kg
3660740027407	-	3660740227401 - 140 pcs
3660740027438	-	3660740227432 - 140 pcs
CUSTOM CODE: 9004901000		

ASSEMBLY RESTRICTIONS

MAXIMUM SPHERE POWER	- 8 / + 6	MAXIMUM CYLINDER	+ 5
----------------------------	-----------	---------------------	-----

LENS MATERIAL / IMPACT RESISTANCE

PC / C	CR39 / -	TRIVEX / C
--------	----------	------------

GENERAL SPECIFICATIONS

LENS	POLYCARBONATE - 2 MM	FOAM	
CURVE	6 - CURVED	STRAP	
FRAME	RECYCLED PC/TPR - METAL BAR	SUPPLIED WITH	MICROFIBER POUCH

OPTIONAL ACCESSORIES

REFERENCE	DESCRIPTION	SINGLE	INNER BOX	OUTER PACK
PSPUNISS01	RETAINER STRAP	3660740011970	3660740111977 - 40 pcs	3660740211974 - 480 pcs

KNOW MORE
ABOUT
MARKINGS:

CLICK

OR SCAN:



CLEANING & STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.**MAINTENANCE:** Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.**STORAGE:** All products must be stored in a dry and clean environment.

MADE IN: CN

DATASHEET: 10-14-2026

bolle-safety.com

Europe Headquarters
34 rue de la Soie
69100 Villeurbanne
France
P : 00 33 (0) 4 78 85 23 64

U.K. & Ireland
Unit C83 - Barwell Business Park
Leatherhead Road - Chessington
Surrey - KT9 2NY - UK
P : 00 44 (0)208 391 4700

USA Office
5355 Avenida Encinas, Suite 107
Carlsbad, CA 92008
United States of America
P : 800 222 6553

Asia-Pacific Office
32-40 Fairchild Street
heatherton VIC 3202
Australia
P : 1300 138 098

THE PPE EYEWEAR
SPECIALISTS