# COVERALL CLEAN & AUTOCLAVE

The COVERALL AUTOCLAVE goggle has been especially developed to guarantee high protection & comfort in risky environments, like pharmaceutics, micro-electronics or even surgery departments.





COVACLAVE



79 g



COVACLEAN



90 g

# **COVACLAVE // COVACLEAN**

- + CLEAN NEOPRENE STRAP
- OVERFLOW CHUTE FOR LIQUIDS
- + FITS OVER PRESCRIPTION SPECTACLES

## COVACLAVE

- **TPR FRAME / UPPER INDIRECT**VENTILATION / SEALED IN THE LOWER PART
- **HIGH-COMFORT AUTOCLAVABLE GOGGLE**
- + �PLATINUM COATING (+P)

## COVACLEAN

- **+ PVC FRAME / UPPER & LOWER**INDIRECT VENTILATION
- + STERILISABLE BY GAMMA & BETA RADIATION



# COVERALL CLEAN & AUTOCLAVE

MODEL	VERSIONS	REFERENCES	LENS MARKING	FRAME MARKING	COATINGS
COVERALL	Ventilated	COVACLEAN	2C-1,2 😭 1 BT €€	≅ EN166 3 4 BT <b>C €</b>	ASAF
	Semi-ventilated	COVACLAVE	2C-1,2 😭 1 FT KN €€	≅ EN166 3 4 FT <b>C€</b>	Anti-scratch/Anti-fog (⁺ <b>P</b> )

### LENS MARKING

Optical class symbols:

1. Continuous work

Mechanical strength symbols:

- B. Medium energy impact, resists a 6 mm, 0.86 g ball at 120 m/s.
- F. Low energy impact, resists a 6 mm, 0.86 g ball at 45 m/s.
- T. The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

Others symbols:

- K. Resistance to surface damage by fine particles
- N. Resistance to fogging
- C€ European standard ☐ Manufacturer name

# TECHNOLOGY



The new exclusive scratch and fog resistant coating guarantees even more safety, reliability and comfort. Washable (water and soap), this permanent coating applied on both sides of the lens makes it highly scratch resistant and durably delays the appearance of fogging.

PACKAGING AND EAN 13 CODE						
	COVACLEAN	COVACLAVE				
Individual plastic bag	3660740007850	3660740000646				
5 safety goggles per box	3660740107857	3660740100643				
105 safety goggles per outer pack	3660740207854	3660740200640				











### ASIA/PACIFIC HEADQUARTERS:

Bollé Australia Ptv Ltd 32-40 Fairchild Street Heatherton VIC 3202 T: 1300 138 098 E: safety@bolle.com.au

### **NEW ZEALAND:**

Bollé New Zealand Limited Unit 5, 114 Sawyers Arms Road Papanui, Christchurch 8052 T: 03 3751400 E: bolle@bolle.co.nz

# FRAME MARKING

EN 166: guaranteed minimum resistance of the protective eyewear against everyday risks including dropping the protective eyewear onto the ground, ageing by light exposure, exposure to heat or corrosion etc.

- 3. Liquid droplets or splashes.
- 4. Large dust particles > 5 microns.
- F. Low energy impact, resists a 6 mm, 0.86 g ball at 45 m/s.
- B. Medium energy impact, resists a 6 mm, 0.86 g ball at 120 m/s.
- T. The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

Bollé Safety product approval certificates to CE standards will be sent on request.

### CLEANING AND STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.

CHARACTERISTICS				
LENSES	PC - 2,2 mm - Curve 4			
FRAME	PVC (CLEAN) / TPR (CLAVE)			
TEMPLES	Non applicable			
STRAP	Adjustable/ Neoprene			
FOAM	No			
MAINTENANCE AND CLEANING	Soapy water			
STERILIZATION COVACLAVE	121° / 20 mn / 15 Cycles			

